

## SL600 Pinnacle™ Premium Stair Lift

- Narrowest stair lift in the industry—only 11" when folded
- Wireless remotes for effortless stair lift accessibility
- Comfortable seat with height adjustment
- Swivel seat at upper landing, for easy and safe entry and exit
- Uses less electricity than a 25 watt light bulb!
- Lightweight unit weighs only 165 lbs (chair and 16ft track)
- Standard unit is 16ft; additional lengths available up to 70ft
- Easily changeable from left or right side of stairway
- No greases or lubricants; easy to vacuum and keep clean
- Easily changeable from left or right side of stairway
- 3-year warranty on components/lifetime warranty on gear rack/1-year warranty on batteries

**PINNACLE** *Seat upholstery colors: Light almond is standard; alpine, ruby or bluebell available as an optional upgrade)*

### Information At A Glance

Easy operating controls and indicator lights



### Safety & Security

Removable key lock for safety when you are away (optional upgrade)



### Unique Drive System

Patented drive system makes more than 2 times the amount of trips on battery power than other leading units



Safety sensors on carriage and footrest stop the lift instantly if an obstacle is encountered

Harmar stair lifts are designed to meet ANSI/ASME A18.1 Performance Safety Standards when properly equipped. While Harmar stair lifts meet national standards, it is imperative to check state and local code requirements before installing to ensure compliance. All state and local compliance is the responsibility of the purchaser. Some states may require fees for site preparation and permits. The Pinnacle should only be installed by a certified, professional Harmar installer. If the stair lift is installed by any other means, the purchaser and installer assume responsibility for issues that may arise involving improper installation.

Minimum folded width	11"
Minimum footrest height	3.5"
Minimum swing length (check knees)	26"
Clear distance between armrests	19"
Floor to seat height—low/high	20"/24.5"
Minimum wall to stair side of rail	6.5"
Seat depth	16"
Backrest height from top of seat	18"
Maximum weight capacity	350 lbs
Electrical requirements	115 VAC
Operation power	24V DC Battery
Maximum travel	70 ft
Speed	17 ft/minute

Incline limits	32–52°
Drive system	Polymer worm/worm-rack
Motor output speed at rated load	62 rpm
Motor output torque at rated load	18 lb/ft
Motor output amps at rated load	14 amps
Track (rail) type	Extruded aluminum
Average number of return trips per charge (varies with load, length)	20–40
Number of tools required to install	5
Symmetrical lift (installs to left or right or stairs)	Yes
Interchangeable arms (left or right hand operation)	Yes
Need to open chassis to install or change sides?	No
Lift mounts to steps or wall?	Steps